



Notes:

1. Material:
 - 1.1 Bobbin: 3510-260 Peek Coil Form
 - 1.2 Magnet Wire: #32 HML (MW16-C), 250 Turns pulled through alcohol bath.
2. Finish:
 - 2.1 Tie knot in Finish wire and twist with Start to anchor.
 - 2.2 Wire must be confined within OD of coil form.
 - 2.3 DCR **should be** 10.6 Ohm nominal.

Unless otherwise specified
 All dimensions are in inches.
 Tolerances: Decimal: x.x ±.25, x.xx ±.01
 x.xxx ±.003
 Angular: x.x ±1°

Coil Assembly

CALIFORNIA INSTITUTE OF TECHNOLOGY MASSACHUSETTS INSTITUTE OF TECHNOLOGY		REV. A
SIZE: B	DWG. NO. 3510-260-1	
SCALE: 1:1	PROJECTION:	SHEET 1 OF 1

Draw2, PART PDM REV: , DRAWING PDM REV: